



Click [here](#) for the 3D model.

## General Information

Series	QFC
Type	Flame Detection
Style	TO39
Description	Analog output flame sensor
Features	High Responsivity, Wide Field of View, Rapid Recovery from Shock, Analog Output
RoHS	With Exemptions
REACH	SVHC (PZT - CAS 12626-81-2)
SCIP Number	3c31b9af-be99-48ff-a8c3-2ea3307a1989
Qualifications	REACH

## Specifications

Temperature Range	-40/+85°C
Power Supply Voltage	2.7 - 8.0 V
Miscellaneous	Sensor Type: Single.
Microphonics	S(vib) ~2 $\mu$ V/sqrt(Hz) (at 10 Hz)
Noise	Mean 70 $\mu$ V sqrt(Hz)
D*	$3.5 \times 10^8$ cm sqrt(Hz)/ W
Time Constant	12ms
Field of View	100 degrees
Element Size	1000um x 1000um
Filter Aperture	5.2mm x 4.2mm
Filter	4.48 um bandpass
Responsivity	150,000 V/W

## Dimensions

L	9.14mm +0.05/-0.06mm
W	9.14mm +0.05/-0.06mm
H	17.3mm +/-1mm
T	3.8mm NOM

## Packaging Specifications

Packaging	Bulk
Packaging Quantity	50
Typical Component Weight	950 mg