
VRR40L104MWS



 $\label{eq:VRR Indust X7R HVHT200C, Ceramic, 0.1 uF, 20\%, 500 VDC, X7R, Commercial, High Temperature, HighVoltage, 6.35 \,mm$



General Information	
Series	VRR Indust X7R HVHT200C
Style	Radial
Description	Commercial, High Temperature, HighVoltage
Features	Commercial
RoHS	No
Prop 65	WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov /
SCIP Number	8b930311-e6ed-4436-9857-2b 5f449be092
Termination	Lead (SnPb)
Lead	Wire Leads
Failure Rate	N/A
Testing and Reliability	Standard
AEC-Q200	No

Dimensions	
L	8.89mm MAX
W	10.16mm MAX
Т	6.98mm MAX
S	6.35mm +/-0.76mm
LL	31.75mm MIN
F	0.635mm +/-0.051mm

0.1 uF
20%
500 VDC
750 VDC
-55/+200°C
X7R
2.5% 1 kHz 1.0Vrms
10 GOhms

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	1

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/18/2025 © 2006 - 2025 YAGEO