



Click [here](#) for the 3D model.

General Information	
Supplier	KEMET
Series	VA
Type	Varistors
Style	SMD Chip
Description	SMD 125C Multilayer Chip Varistor, 12V Power Supply
Features	Automotive
Termination	Nickel Tin
RoHS	With Exemptions
Qualifications	IEC, AEC-Q200
AEC-Q200	Yes

Specifications	
Voltage DC	20 VDC (25C)
Voltage AC	17 VAC
Temperature Range	-55/ +125°C
Storage Temperature Range	-55/ +150°C
Varistor Voltage	27 VDC at 1 mA
Jump Start Voltage	30 VDC (5 min)
Clamping Voltage	44 V
Clamping Current	5 A (8/20 us MAX)
Surge Current	800 A (8/20 us MAX)
Energy	2.9 J (10/1000 us MAX)
Load Dump	6 J
Power	0.015 W (MAX)
Capacitance	3.8 nF (1kHz)

Dimensions	
Chip Size	1812
L	4.7mm +/-0.4mm
W	3.2mm +/-0.3mm
T	1.3mm
B	0.5mm +/-0.25mm

Packaging Specifications	
Packaging	T&R
Packaging Quantity	1000

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.