



Click [here](#) for the 3D model.

Dimensions

Chip Size	0402
L	1mm +/-0.05mm
W	0.5mm +/-0.05mm
T	0.5mm +/-0.05mm
B	0.25mm +/-0.1mm

Packaging Specifications

Packaging	T&R
Packaging Quantity	10000

General Information

Series	Z-PMS
Style	SMD Chip
Description	Chip Bead, Power Line
Features	Increases The Z Characteristics Sharply Above 20MHz And Is Applicable For Radiated Noise In The 100MHz-300MHz Range, Especially Effective On Video Signals
RoHS	Yes
Notes	Suggested Replacement - https://productfinder.pulseelectronics.com/part/BBPY00100505121Y00 .

Specifications

Impedance	220 Ohms (100 MHz)
Impedance Tolerance	25%
Ripple Current	900 mA (MAX)
Temperature Range	-55/+85°C
DC Resistance	0.18 Ohms