


[Click here for the 3D model.](#)

General Information

Series	VRR Indust X7R HVHT200C
Style	Radial
Description	Commercial, High Temperature, High Voltage
Features	High Temperature, High Voltage, Commercial
RoHS	With Exemptions
REACH	SVHC (Pb – CAS 7439-92-1)
SCIP Number	d1f8aba3-2564-4904-a1cf-714fe85ef1ab
Termination	Gold
Lead	Wire Leads
Failure Rate	N/A
Testing and Reliability	MIL-PRF-20 Group A
Qualifications	MIL-PRF-20 Group A
AEC-Q200	No

Dimensions

L	7.62mm MAX
W	7.62mm MAX
T	3.81mm MAX
S	5.08mm +/-0.76mm
LL	31.75mm MIN
F	0.635mm +/-0.051mm

Specifications

Capacitance	1,000 pF
Tolerance	10%
Voltage DC	2000 VDC
Dielectric Withstanding Voltage	3,000 VDC
Temperature Range	-55/+200°C
Temp. Coefficient	X7R
Dissipation Factor	2.5% 1 kHz 1.0Vrms
Insulation Resistance	100 GOhms

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	1

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.