



Click [here](#) for the 3D model.

#### Dimensions

Chip Size	0603
L	1.6mm +/-0.1mm
W	0.8mm +/-0.1mm
T	0.8mm +/-0.1mm
B	0.3mm +/-0.15mm

#### Packaging Specifications

Packaging	T&R
Packaging Quantity	4000

#### General Information

Series	Z-PWZ
Style	SMD Chip
Description	Chip Bead, Power Line
Features	For MHz Range Applications
RoHS	Yes
Notes	Last Order Date June 30, 2023. Suggested Replacement - <a href="https://productfinder.pulseelectronics.com/part/BBPY00160808331Y00">https://productfinder.pulseelectronics.com/part/BBPY00160808331Y00</a> .

#### Specifications

Impedance	330 Ohms (100 MHz)
Impedance Tolerance	25%
Ripple Current	900 mA (MAX)
Temperature Range	-40/+125°C
DC Resistance	0.13 Ohms