

Z0805C331APMST

Aliases (Z0805C331APMST)


General Information

Obsolete

Series

Style

EMI Suppression, KEMET, Z-PMS, SMD Chip, Noise Suppression



T	Description	Chip Bead, Power Line
	Features	Suppresses The XL Component; Helps Stop The Reduction Of The Wave-Form Integrity
	RoHS	Yes

Click here for the 3D model.

Dimensions	
L	2mm -3mm
W	1.25mm +/-0.2mm
Т	0.85mm +/-0.2mm
В	0.5mm +/-0.3mm

Packaging Specifications		
Packaging	T&R	
Packaging Quantity	4000	

Specifications	
Impedance	330 Ohms (100 MHz)
Impedance Tolerance	25%
Ripple Current	1500 mA (MAX)
Temperature Range	-55/+85°C
DC Resistance	0.075 Ohms

Z-PMS

SMD Chip

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/05/2025 © 2006 - 2025 YAGEO